



Transparent cover BLine Select SX10

BLine Select SX10 cover transparent flat 2000 mm for XT01_02_03

Article no.: 170403



Covering width



Bore/transmittance



Net height

TENDER TEXT

Cover XT, transparent flat, 120x120, 85%, PMMA, L 2000 x W 23 x H 7.4 mm BILTON LEDON Technology Transparent cover BLine Select SX10 Article 170403 The Transparent cover BLine Select SX10 cover can be combined with all profiles from the XT family The cover consists of Kunststoff and has a transparent finish with a transmittance degree of 85 %. Easy installation via into the profile. Dimension (L x W x H): 2000.0 mm x 23.0 mm x Please note that cutting tolerances of +/- 2mm may occur.

Transparent cover BLine Select SX10

BLine Select SX10 cover transparent flat 2000 mm for XT01_02_03

Article no.: 170403



MECHANICAL DATA

Material	Kunststoff
Width [mm]	23.0
Length [mm]	2000.0
Covering width [mm]	23
Colour	ohne
Model	Lengthwise cover
Suitable for	U - Profil
Inflammability class of insulation material acc. with UL94	HB
Surfacetreatment	transparent
Bore/transmittance [%]	85

TEMPERATURE TECHNICAL DATA

Ambient/storage temperature [°C]	+ 10 ... + 50
Inflammability class of insulation material acc. with UL94	HB
Thermal conductivity	70
Bore/transmittance [%]	85

PACKAGING INFORMATION

EAN	4250716919660
Article no.	170403
Net weight [g]	88.8
Gross weight [g]	88.8
Gross width [mm]	23.0
Gross height [mm]	7.4
Gross length [mm]	2000.0
Customs tariff number	94054231
Net width [mm]	23.0
Net height [mm]	7.4
Net length [mm]	2000
State of origin	IT

SAFETY INFORMATION: Read the safety and installation instructions carefully and completely before commissioning. The operating instructions can be found at: www.better-light.at

DISCLAIMER OF WARRANTY: The technical information corresponds to the status at the time of printing and have been worked out to the best of our knowledge. However, errors and printing errors are reserved. Make sure that you always use the latest version of the data sheets. The latest data sheet can be found at: www.better-light.at