

Downlight Protected

LED DRIVER 220-240V CC 450mA 27-45VDC ON/OFF Protected DL

Article no.: 729165



ohne

Control signal

IP20

Degree of protection (IP)

450

mA

Output current range

TENDER TEXT

for DL Protected 145mm BILTON LEDON Technology Downlight Protected Article 729165 The power supply can be used for a output voltage range of 27-45 V. Constant current 450 mA. The supply voltage of the power supply is 198 - 264 V and has a IP20 protection type and protection class II . Control signal ohne . Dimensions (L x W x H): 137.5 mm x 44.0 mm x 23.0 mm



Downlight Protected

LED DRIVER 220-240V CC 450mA 27-45VDC ON/OFF Protected DL

Article no.: 729165



MECHANICAL DATA

Housing	Kunststoffgehäuse
Width [mm]	44.0
Length [mm]	137.5
Height [mm]	23.0
Model	Static
Control signal	ohne
With overheating protection	nein
Suitable for outdoor use	nein
Degree of protection (IP)	IP20
Core cross section [mm ²]	0,5 - 1,5

ELECTRICAL DATA

Protection class	II
Control signal	ohne
With overheating protection	nein
Input voltage range [V]	198 - 264
Output voltage range [V]	27 - 45
Output current range [mA]	450
Overload protection	Yes
Standby power consumption (solstandby) [W]	0.5
Suitable for constant current	Yes
Suitable for constant voltage	nein
Suitable for DC-voltage (primary side)	Yes
No dim function	Yes

CONNECTION

Core cross section [mm ²]	0,5 - 1,5
---------------------------------------	-----------

TEMPERATURE TECHNICAL DATA

Ambient/storage temperature [°C]	- 40 ... + 85
Ambient temperature during operating [°C]	- 20 ... + 45

PACKAGING INFORMATION

EAN	4250716950953
Article no.	729165
Customs tariff number	85044083
Net width [mm]	44.0
Net height [mm]	23
Net length [mm]	137.5
State of origin	CN

Downlight Protected

LED DRIVER 220-240V CC 450mA 27-45VDC ON/OFF Protected DL

Article no.: 729165



SAFETY INFORMATION: Read the safety and installation instructions carefully and completely before commissioning. The operating instructions can be found at: www.better-light.at

DISCLAIMER OF WARRANTY: The technical information corresponds to the status at the time of printing and have been worked out to the best of our knowledge. However, errors and printing errors are reserved. Make sure that you always use the latest version of the data sheets. The latest data sheet can be found at: www.better-light.at